

# C & tan $\delta$ Meter for Insulation Materials **DAC-IM-D6**



DAC-OBE-2

DAC-IM-D6 measures capacitance and the dielectric loss tangent (tan  $\delta$ ) of electrical insulating materials with resolution of 1 ppm (1 × 10<sup>-6</sup>).

Measurements in accordance with IEC standards (IEC 60247 and IEC 60554-2) are available by using with an optional liquid or sheet or other appropriate electrode. Furthermore, the relative permittivity of an insulating material can be displayed by saving the capacitance of an empty electrode into memory.

#### Features

- Best resolution for measurement of tan  $\delta$ : 0.0001% (1 ppm)
- Output voltage source, built-in power supply for testing: AC 200 V to 2100 V (50/60 Hz)
- Display relative permittivity data from the result of capacitance measurements
- Auto-range provided for capacitance and tan δ measurements with automatic step-up of voltages
- USB interface provided as standard equipment

Test Specimen

Electrical insulating oil Electrical insulating (ceramic, polymeric) materials Other dielectric materials

# SOKEN ELECTRIC CO., LTD.

# DAC-IM-D6 C AND TAN $\delta\,$ METER FOR INSULATION MATERIALS

DAC-IM-D6 is ideal for testing electrical characteristics of electrical insulating materials, such as oil, ceramic, polymeric, etc.

The meter can be applied to the test in accordance with JIS (C2101) and IEC (60247, 60554-2) standard, and is also utilizable for development tests of new and composite materials.

DAC-IM-D6 is contains a built-in testing voltage supply (Max 2000V), and allows measurement of tan $\delta$  and capacitance with applying the actual voltages to specimens, which helps identify the actual electrical characteristics.

Repeated measurement is possible through simple operating steps. In addition, data can be collected from external PCs through USB interface.

#### **Specifications**

•	Built-in power supply:	0 - 2100 VAC, 50/60 Hz		
		(test frequency cha	nged manually)	
•	Measurement range:	Measuring voltage	:0 - 2000 V, 50/60 Hz	
		Capacitance	:20 - 1000 pF (2 ranges: automatic range)	
		tan δ	:0 - 50% (4 ranges: auto/manual range)	
		Relative permittivity	y:0.02 - 50.0	
•	Minimum resolution:	Measuring voltage	:1 V	
		Capacitance	:0.1 pF	
		tan δ	:0.0001% (1 ppm)	
		Relative permittivity	y:0.01	
•	Measuring accuracy:	Measuring voltage	:± (0.5% rdg + 2 digits)	
		Capacitance	:± (0.5% rdg + 2 digits)	
		tan δ	:± (0.001% + 1% rdg + 2 digits)	
		Relative permittivity	y:± (1% rdg + 2 digits)	
•	Interface:	USB 2.0/1.1 compl	iance, B-type connector	
•	Input power source:	100 - 240 VAC ± 10	0%, 50/60 Hz	
•	Dimensions and weight:	430 (W) × 200 (H)	× 380 (D) mm, about 13 kg	
•	Standard Accessory:	Measuring Cable w	ith connector/Clip 1 set	
		AC Power Cable, G	Ground Wire, Storage Bag	

#### LCD Panel



# SET MODE Functions

When SET MODE is selected, you can set the following three parameters. These settings are saved in a nonvolatile memory, and will be available when the Meter power is turned on again, later.

- Test voltage (0 to 2000 V)
- Test frequency (50/60 Hz)
- Electrode without sample (20 to 1000 pF)



#### **Option Accessories**

#### Liquid Electrode Model DAC-OBE-2

DAC-OBE-2 is an electrode for testing electrical insulating oil and other liquid insulating materials in accordance with the JIS (C2101) standard.

It is applicable to dielectric loss tangent tests and volume resistivity tests.

Electrode spacing	:	1 mm±0.1 mm (IEC 60247)
<ul> <li>Electrode area</li> </ul>	:	100 cm <sup>2</sup>
Electrode constant	:	1000±50 cm
Capacitance	:	88.5 pF±5 pF
Sample volume used	:	50 cc
• Dimensions & Weight	:	$89.5\phi \times 105$ (mm) Approx. 1.3 kg
Option accessory	:	Adaptor & Cable

#### ■Liquid Electrode Heater Model DAC-OBH series

DAC-OBH series heat the liquid Electrode DAC-OBE-2 (1, 2 or 4 pcs) without using thermal oil.

The uniform heat conductivity eliminates possible differences in temperature between each electrode. Combining a controller, Nominal temperatures are maintained within  $\pm 1^{\circ}$ C, ensuring conformity to JIS C2101.

- Made of High Purity Aluminum Heater.
- •No thermal oil is required.
- Splash-free, vaporization-free and air pollution-free measurement
- Quick clean-up after use
- •Eliminated local heating, Heat is distributed evenly.

Model	DAC-OBH-1	DAC-OBH-2	DAC-OBH-4		
Number of electrodes	1	2	4		
Allowable maximum setting temperature	Max. 100°C (Setting temp.±1°C)				
Input power	AC 100 V/200 V 50 Hz/60 Hz				
Power consumption	500 W	800 W	1500 W		
Dimensions (mm)	W190xD190xH160	W360xD190xH160	W360xD360xH160		
Weight	5 kg	9 kg	18 kg		
Dimensions & Weight of Controller	W210xD292xH250 (mm), 3.5 kg				



DAC-OBE-2



Adaptor & Cable for DAC-OBE-2



DAC-OBH-4

# DAC-IM-D6 C & tano Meter for Insulation Materials

# Electrode for Solid Materials Model DAC-OBE-7

An electrode DAC-OBE-7 can be used for measuring permittivity and dielectric loss tangent of insulating paper, film and other insulating materials in accordance with JIS standard (C2111). The electrode is equipped with a cylinder to reserve insulating oil, and designed to withstand temperatures of up to 120°C.

Electrode :	Main electrode	;	65.5φ (mm)	
	Guard electrod	le	66ø (mm)	
	High-voltage e	lectrode	84ø (mm)	•
	Material Stain	less stee	1	
Test voltage:	Max. 10 kV			
	<1kV	: No insu	lating oil is necessary.	
	1kV to 5kV	: Fill insu	lating oil in the cylinder.	
	5kV to 10kV	: Fill insu	lating oil in the cylinder and	
		submer	ge the electrode entirely in oi	l bath.
Test temperatur	re: Max. 120°	°C		
	t. Annual 2	F0		

- Cylinder Capacity: Approx. 350 cc
- Dimensions : H210 × 150¢ (mm)

# Electrode for Sheet Materials Model DAC-OBE-8

DAC-OBE-8 is designed for measurement of permittivity, dielectric loss tangent, and insulation resistance of insulating paper, plastic films, and other sheet Materials.

Electrode :	Main electrode	78ø (mm)	
(JIS K6911)	Guard electrode	80ø (mm)	
	High-voltage electr	rode 100ø (mm)	
Material Stainless steel			
	(The other Electrode	sizes: on inquiry)	
Test voltage	e: Max. 1 kV		

Dimensions: W190 × H105 × D190 (mm)

# **The setimate of the set Model DAC-Cs-100A The set Model DAC-Cs-100A**

DAC-Cs-100A accommodates a gas-filled standard capacitor of 100pF capacitance, and is used to calibrate DAC-IM-D6 by utilizing commercial frequencies 50, 60Hz.

Integrated reference capacitor: Gas filled capacitor of 100 pF

Working voltage:	AC 2000 V
Capacitance :	100pF
• tan $\delta$ calibration value:	0 to 8.0% at 50 Hz
	0 to 9.6% at 60 Hz
Dimensions & Weight:	W200 × H177 × D233 (mm)
	Approx. 4.5 kg



DAC-OBE-7



DAC-OBE-8



DAC-CS-100A

$\overline{}$	50Hz		60Hz		
1	0.0000	%	0.0000	%	
2	0.0020	%	0.0024	%	
3	0.0080	%	0.0096	%	
4	0.0800	%	0.0960	%	
5	0.800	%	0.960	%	
6	8.00	%	9.60	%	

tan  $\delta$  Calibration Value

2022/09/09



1-34-22, Tobitakyu, Chofu Tokyo 182-0036 JAPAN

TEL: 81 42 490 6929 (Export Dept) FAX: 81 42 490 6807 www.soken-jp.com

